



TECHNICAL DATA SHEET

JELTOSEC

Electronics

7321 - JELTOSEC.doc

1. OUTSTANDING FEATURES

JELTOSEC is a dry cleaning degreaser with fast evaporation, for the cleaning of all the electric or electronic contacts. It cleans all the polar spots, fat deposits and other organic residues. It eliminates the residue on printed circuits, without leaving either track or deposit. It can be used on plastics and markings.

2. TYPICAL APPLICATIONS

JELTOSEC is ideal for the cleaning of :

- Electronic sets,
- Electric cupboards,
- Cursors, connectives, switches, components,
- Electric contacts...

3. DIRECTIONS FOR USE

Well shake the aerosol. Place the capillary tube on the diffuser. Vaporize by brief and repeated pressures on the surface. Let act. Renew the operation if necessary. Wait for some minutes before switching the equipment on after use.

4. PHYSICAL AND CHEMICAL PROPERTIES

Active Ingredient :

- Appearance : Colorless crystal clear liquid
- Smell : Of solvents
- Volume mass @ 20°C : 0.68 g/cm³
- Very flammable

5. USAGE INSTRUCTIONS

Pressurized container. Consult the safety data sheet. Do not smoke. Skin Irritant. Do not vaporize towards a flame or an incandescent body. Do not throw to the fire. Keep out of reach children. Do not inhale sprayers. Well ventilate after usage.

6. PACKAGING AND STORAGE

Reference 7321: 520 ml aerosol (12 aerosols per box).

To protect from sun and do not expose to temperatures exceeding 50°C. Keep away from any flame or source of sparks or of ignition. Do not drill or burn after usage. Store in a dry place and in a ventilated area. Store at a temperature over 5°C.

This technical sheet was issued on 23/05/2001 and cancels any previous information. The information herewith provided is based on our today's knowledge and experience. We do not guarantee the accuracy of the data and assume no liability in connection with damages incurred while using this product.

ITW Produits Chimiques 99 Quai du Docteur Dervaux 92600 ASNIÈRES SUR SEINE-FRANCE ☎ (33)1.40.80.32.32 Fax (33)1.40.80.32.30